

MICROMAC NITRATE UV REDUCTION ON LINE ANALYZER FOR NITRATE MONITORING IN WATER



MICROMAC NITRATE is a microprocessor controlled On Line analyzer specifically designed for automatic Nitrate monitoring on several types of water matrix.

✓ ROBUST AND RELIABLE

Designed for industrial and Environmental On Line applications Micromac C ensures the highest level of robustness in the electronics, mechanics and hydraulics components. Complete separation between electronics and hydraulics plus a simple and robust LFA * hydraulics allows easy maintenance and long terms reliable operations.

** LFA: Loop Flow Analysis patent pending*

✓ EASY TO INSTALL

The analyzer is delivered after a long and successful series of factory tests ready for installation and setup; it is provided with complete set of spares for start up. To start monitoring is enough to connect reagents, sample line, waste line and power supply.

✓ AUTOMATIC CALIBRATION

When the Calibration Time interval expires the analyzer performs a Calibration Cycle, storing and checking the new calibrant O. D. If new O.D. exceeds selected limits, an alarm contacts is closed.

✓ SAMPLE DILUTION

Sample can be analyzed as it is or after automatic dilution. Automatic dilution is factory adjusted for high range applications.

✓ MEASURING INTERVAL


User selectable; between two measurements the analyzer remains in stand by mode, without reagents consumption.

✓ FEATURES AND BENEFITS

- Fully automatic operation
- Long autonomy; low maintenance, low operating cost
- Low reagents consumption; short preparation time; low disposable costs
- Easy operation; plug in analyzer, no special training is required
- Electronics and hydraulics completely separated
- Serial interface for local o remote PC connection (option)

Nitrate measuring principle and hydraulic diagram

The sample after proper filtration is pumped inside the LFA reactor, where the photoreduction reagent is added in presence of UV radiation, to convert the nitrate contained in the sample into nitrite. The microprocessor starts the reagents addition sequence taking and storing as first the sample blank, then nitrite contained in the sample reacts with a solution of NED+SAA to develop a reddish color; after a further mixing step and a proper reaction time, the complex is measured at 525 nm. The sample concentration is calculated against the calibration factor stored in the analyzer.



Technical Specifications

MEASURING PRINCIPLE: Colorimetric, UV photoreduction to NO₂, colorimetric reaction with NED+SAA

COLORIMETER: dual beam, silicon detector

MEASURING TYPE: cyclic

MEASURING INTERVAL: programmable **MEASURING TIME:** 13-15 minutes depending on the range

MEASURING RANGE: 0-5/10/20/100/200/1000 ppm N-NO₃, other ranges available on request

DETECTION LIMIT: typically better 3% of the full scale, calculated as for EPA p. 136 appendix B

REPEATABILITY: better than 3%

OUTPUT SIGNAL: 4-20 mA

INPUT SIGNALS: n. 1 Analysis, n. 1 calibration; digital contacts

ALARMS: n. 1 High Limit, n. 1 General, n. 1 Calibration; potential free contacts

SAMPLE AND WASTE DELIVERY: pressure free;

REAGENTS REPLACEMENT: 3/4 weeks depending on the operating temperature

SAMPLE TEMPERATURE: 10 °C - 30 °C

PROTECTION: IP55

HARDWARE: PC104 industrial standard, Integrated keyboard and graphics display, RS232 option

POWER SUPPLY: 12 V DC; external power supply from local power to 12 V DC included

WEIGHT: 33 Kg without reagents; **DIMENSION:** 800x450x300 mm(hxwx d)

Subject to change without notice



SYSTEA S.p.A.

HEADQUARTER AND MANUFACTURING FACILITY:

VIA PADUNI, 2A - 03012 ANAGNI (FR) ITALY

TEL: +39 0775-776058 FAX +39 0775-772204

A member of Consorzio NDI

Web Site: <http://www.systea.it> Email: info@systea.it

Document ID: MicC_Nitrate UV-02-E